

Innova

Innova 20 / 30 / 40 / 50 is a perforated pressure sensitive window film designed for mid-term applications (up to 3 yrs). This product offers a full range of 20%, 30%, 40% and 50% open area. PanoramalInnova is a high quality European & USA best seller at budget pricing

APPLICATIONS

- * Retail & corporate windows
- * Building wraps
- * Car, bus, train & tram windows
- * All applications up to 3 years

ADVANTAGES

- * Printable on Solvent, UV & Latex
- * 3 year durability applied under normal conditions
- * Calendared vinyl features with great dimensional stability
- * Special "Universal Liner" enables easy handling during application



Innova

MATERIAL

- * Perforated calendered vinyl film
- * 145 micron
- * Self adhesive
- * Printable white front side
- * Black reverse side for maximum contrast
- * Removable, semi permanent clear adhesive
- * Excellent dimensional stability

LINER

- * 4mil universal paper liner

OPEN AREA / PRINTABLE AREA PRODUCTS

Innova20 - Open area 20% / Printable area 80%
Innova30 - Open area 30% / Printable area 70%
Innova40 - Open area 40% / Printable area 60%
Innova50 - Open area 50% / Printable area 50%

APPROVALS

German TUV - D5453, - D 5307 and - D 5452

PRINTING METHOD

Digital - Solvent / UV / Latex
Screen Print

FLAMMABILITY

M1, B1 & ASTM E84 certified

HUMIDITY & SOLVENT RESISTANCE

Good

APPLICATION TEMPERATURE

+10°C to +30°C (+50°F to +86°F)

SERVICE RANGE TEMPERATURE

-17°C to +50°C (+0°F to +122°F)

SHELF LIFE

1 year, stored at +15 to +20° C (59 to 68° F)
and relative humidity between 45 and 65%.

DURABILITY

Up to 3 years in normal conditions. Clean removal within 6 months. Tack may increase over time. Not to be applied on: fresh paint or ink, polycarbonate, certain PVC (no exhaustive list). For critical substrates, please test prior to application.

APPLICATION

Prevent from contact with solvent or ammonia based cleaner. Clean window with soap and water. Rinse and dry glass after cleaning. ALWAYS clean and dry glass prior to application. Please respect our application instructions.

